


Gilt ab Gerdt Nr. 1001

Nennspannungen der Keramik-Kondens. MP-Kondens.			Elkos	
500V =	3V	250V	280V	450V
Pos. 1	30	31, 32	33	34, 35, 36, 37, 38



Werkstoff:

Br.-Bauh.Nr.	V 72
Br.	172.8.81
Kontak.	/
Qapp.	/
Qansh.	Y. 7. 1. 1.
Zählung.Nr.	

Studoverstärker

S 843

Ang. & Bn. 1 | Blatt